

# AM7515MT8A



**Marke:**

**Artikelnummer:** AM7515MT8A

## Short Description

5 Megapixel resolution

700-900x Magnification

Coaxial and brightfield illumination

Flexible LED Control (FLC)

Automatic Magnification Reading (AMR)

## Beschreibung

The AM7515MT8A is a 5MP Dino-Lite Edge Series microscope that has a magnification range of 700-900x with built-in coaxial illumination. By using the Flexible LED Control (FLC), this model is capable of switching between or mixing, brightfield and coaxial illumination.



USB 2.0



Measurement  
functionality



Adjustable  
~700-900x



Flexible  
LED control



Automatic  
Magnification  
Reading (AMR)




Magnification  
lock



5 megapixel  
2592 x 1944



8 White LEDs  
switchable



Exchangeable  
cap



Metal  
housing

The coaxial illumination technique reveals details that are very difficult to see under normal light, for example when inspecting wafer plates, microchips or other microelectronics. The AM7515MT8A includes the Automatic Magnification Reading (AMR) feature which automatically detects and displays the magnification in the included Dino-Lite software. These unique features make the Dino-Lite AM7515MT8A a great inspection tool for material analysis, electronics inspection, or any similar application that requires high magnification, coaxial illumination, versatility and mobility.

The Dino-Lite AM7515MT8A is bundled with the user-friendly DinoCapture 2.0 software for Windows. For this model it includes functions such as Automatic Magnification Reading (AMR), Flexible LED Control (FLC), calibration, measurement, capturing & annotating images, and recording video. When focusing at such high magnification it is recommended to use a high-precision stand. The Dino-Lite RK-10A for example is a great add-on, it is a sturdy and stable high-end stand solution constructed of resilient stainless steel and lightweight aluminum and offers a very precise fine-focus adjustment.

#### Working distance/field of view/depth of field

| MAGNIFICATION RATE                | WORKING DISTANCE*  | FIELD OF VIEW(X) | FIELD OF VIEW(Y) | DEPTH OF FIELD |
|-----------------------------------|--------------------|------------------|------------------|----------------|
| 700                               | 6.4                | 0.56             | 0.400            | 0.01           |
| 750                               | 6.3                | 0.52             | 0.375            | 0.01           |
| 800                               | 6.1                | 0.48             | 0.350            | 0.009          |
| 850                               | 6.0                | 0.46             | 0.330            | 0.009          |
| 900                               | 5.9                | 0.43             | 0.315            | 0.008          |
| Listed values may differ slightly | *Without front cap |                  |                  | Unit = mm      |

## Spezifikation

|                                   |                                                                       |
|-----------------------------------|-----------------------------------------------------------------------|
| Lighting                          |                                                                       |
| Light/ LED type                   | White                                                                 |
| Number of LEDs                    | 8                                                                     |
| LED on/off switchable:            | Yes                                                                   |
| Infrared filter                   | IR cut-filter >650 nm                                                 |
| Diffuser available                | No                                                                    |
| Emission filter                   | No                                                                    |
| Polarizer                         | No                                                                    |
| Optics                            |                                                                       |
| Magnification                     | 700x ~ 900x                                                           |
| Macro zoom                        | No                                                                    |
| Working distance                  | Standard                                                              |
| Lens type                         | Glass with anti-reflection coating                                    |
| Sensor                            |                                                                       |
| Sensor type                       | CMOS                                                                  |
| Resolution                        | 5.0 Megapixel (2592x1944)                                             |
| Maximum frame rate                | 30 fps (max 20fps video recording)                                    |
| Compatibility                     |                                                                       |
| Interface                         | USB 2.0                                                               |
| Operating system                  | Windows 7, 8, 10 & 11, MacOS 10.12 and up                             |
| Software                          | DinoCapture 2.0 (Windows), DinoXcope (Mac OS)                         |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF                                                         |
| Supported image formats (MacOS)   | JPEG, PNG                                                             |
| Supported video formats (MacOS)   | MOV (max 1.3MP)                                                       |
| Imaging standards                 | DirectShow, UVC                                                       |
| Wifi                              | Wireless-ready, requires the WF-10 WiFi streamer (optional)           |
| Housing                           |                                                                       |
| Housing material                  | Metal housing                                                         |
| Magnification lock                | Yes                                                                   |
| Dimensions                        | 10.7cm (L) x 3.2cm (D)                                                |
| Weight                            | 139g                                                                  |
| Cable length                      | 1.8m                                                                  |
| Features                          |                                                                       |
| Special feature                   | Automatic Magnification Reading (AMR),                                |

|                      |                                                                                                          |
|----------------------|----------------------------------------------------------------------------------------------------------|
|                      | Flexible LED Control (FLC), Coaxial illumination                                                         |
| Measurement          | Yes                                                                                                      |
| Calibration          | Yes                                                                                                      |
| Microtouch sensor    | Yes                                                                                                      |
| ESD safe             | Yes                                                                                                      |
| <b>Information</b>   |                                                                                                          |
| Package contents     | Microscope, Carry pouch, software CD, user manual, quick guide, calibration target, front cover box      |
| Warranty information | 2 years European warranty                                                                                |
| Regulatory approval  | CMOS, UKCA – available upon request – <a href="mailto:marketing@dino-lite.eu">marketing@dino-lite.eu</a> |
| Price range          | €1000,00 - €1300,00                                                                                      |

## **Product Gallery**