

AM4517MT-CFVW

Marke:

Artikelnummer: AM4517MT-CFVW



Short Description

1.3 Megapixel Edge sensor

High Sensitivity Sensor



Fluorescence

Automatic Magnification Readout (AMR)

Robust Metal Housing

Beschreibung

Detect a range of fluorophores from cyan to red with the AM4517MT-CFVW high-sensitivity 20x ~ 220x digital microscope. Using 400 nm excitation lights and a 420 nm ~ 650 nm emission filter, this model is suitable for a wide range of probes such as Hoechst 33342, GFP, and Alexa Fluor 405. This model features AMR to ease measurements.



The main features of the AM4517MT-CFVW are:

- 1.3 Megapixel
- High Sensitivity Sensor
- Wide-Ranging Fluorescence Detection
- Switchable White Light
- Automatic Magnification Readout (AMR)
- Robust Metal Housing

Optical Data Table

Magnification Rate	Working Distance *	Field of View(x)	Field of View(y)	Depth of Field
--------------------	--------------------	------------------	------------------	----------------

Listed values may differ slightly	* Without front cap			Unit = mm
20x	60.3	19.53	14.65	6.34
30x	33.6	13.02	9.77	3.03
40x	20.9	9.77	7.33	1.82
50x	13.9	7.81	5.86	1.24
60x	9.7	6.51	4.88	0.91
70x	7.1	5.58	4.19	0.71
80x	5.5	4.88	3.66	0.57
90x	4.0	4.34	3.26	0.47
100x	4.1	3.91	2.93	0.40
110x	3.6	3.55	2.66	0.35
120x	4.1	3.26	2.44	0.31
130x	4.5	3.01	2.25	0.27
140x	5.0	2.79	2.09	0.24
150x	5.6	2.60	1.95	0.22
160x	6.3	2.44	1.83	0.20
170x	7.1	2.30	1.72	0.18
180x	8.0	2.17	1.63	0.17
190x	8.9	2.06	1.54	0.16
200x	9.9	1.95	1.47	0.15
210x	10.9	1.86	1.40	0.14
220x	12.0	1.78	1.33	0.13

Spezifikation

Lighting	
Light/ LED type	400nm excitation + white
Light/ LED type	€1200,00 - €1400,00
Number of LEDs	7 FL + 1 White
LED on/off switchable:	Yes
Infrared filter	No
Diffuser available	No
Emission filter	420 nm ~ 650 nm
Polarizer	No
Fluorophores	Hoechst 33342, GFP, and Alexa Fluor 405
Optics	
Magnification	20x ~ 220x
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	

Sensor type	CMOS
Resolution	1.3 Megapixel (1280 x 960)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Housing	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	104 mm (H) x 32 mm (D)
Weight	Approx. 92 g
Cable length	1.8m
Features	
Special feature	Automatic Magnification Readout (AMR)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
Information	
Package contents	Microscope, carry pouch, calibration target, user manual, N3C-C (Close Cap) N3C-EB (Extended Open Black Cap) N3C-LB (Black Long Cap) N3C-OB (Black Open Cap)
Warranty information	2 years European warranty
Regulatory approval:	CE, FCC, ROHS