

AM8517MZT

Codice del prodotto: AM8517MZT Edge Plus



Short Description

High Optical Resolution

8.0 Megapixel

Enhanced Flexible LED Control (eFLC)

Automatic Magnification Reading (AMR)

Robust Metal Housing

Descrizione

Capture vibrant and true-to-life images with the 8-megapixel Dino-Lite AM8517MZT digital microscope. Including a polarizer and featuring AMR and eFLC, AM8517MZT provides the versatility to perform a variety of tasks.



Metal
housing



Enhanced Flexible
LED control



Adjustable
~10-220x




8,0 Megapixels
3840 x 2160



Measurement
functionality



8 White LEDs
switchable



Polarizer
anti-reflection



Automatic
Magnification
Reading (AMR)

The main features of the AM8517MZT are:

- 8 Megapixels
- High Optical Resolution
- Automatic Magnification Reading (AMR)
- Enhanced Flexible LED Control (eFLC)
- Adjustable Polarizer
- Robust Metal Housing
- 10x ~ 220x magnification (Edge shading occurs below 25x when previewing in 16:9 windows.)
- And more...

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	142.6	60.69	34.14	26.15
20	59.8	30.35	17.07	7.05
30	33.1	20.23	11.38	3.36
40	20.5	15.17	8.53	2.02
50	13.4	12.14	6.83	1.38
60	9.2	10.11	5.69	1.01
70	6.7	8.67	4.88	0.79
80	5.1	7.59	4.27	0.64
90	4.1	6.74	3.79	0.53
100	3.7	6.07	3.41	0.45
110	3.6	5.52	3.10	0.39
120	3.7	5.06	2.85	0.34
130	4.1	4.67	2.63	0.30
140	4.5	4.34	2.44	0.27
150	5.2	4.05	2.28	0.25
160	5.9	3.79	2.13	0.22
170	6.7	3.57	2.01	0.21
180	7.5	3.37	1.90	0.19
190	8.5	3.20	1.80	0.18
200	9.4	3.03	1.71	0.16
210	10.5	2.89	1.63	0.15
220	11.5	2.76	1.55	0.14

Listed values may differ slightly

* Without front cap

Unit = mm

Specifiche

Lighting	
Light/ LED type	White

Number of LEDs	8
Optics	
Magnification	10x ~ 220x
Working distance	142.6 ~ 11.5 mm
Sensor	
Sensor type	CMOS
Resolution	8.0 Megapixel (3840x2160)
Maximum frame rate	10 fps at 8.0 MP, MJPEG 25 fps at 2.0 MP, MJPEG
Compatibility	
Interface	USB 2.0
Operating system	Windows 10/11
Supported image formats (Windows)	BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Supported video formats (Windows)	WMV, FLV, SWF
Housing	
Housing material	Metal housing
Dimensions	130 mm (H) x 33 mm (D)
Weight	120 g
Features	
Special feature	Auto and Manual Refocus
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
Information	
Package contents	N3C-C (Close Cap) N3C-D (Diffuser Cap) N3C-D2 (Opal Diffuser Cap) N3C-E (Extended Open Cap) N3C-L (Long Cap) N3C-O (Open Cap) N3C-S (Sidelight Cap)
Warranty information	2 years European warranty
Regulatory approval:	CE, FCC, ROHS
Price range	€1200,00 - €1400,00