

AM8517MT-FV



Marca:

Codice del prodotto: AM8517MT-FV

Short Description

8.0 Megapixel

High Sensitivity Sensor

Adjustable LED Intensity

Automatic Magnification Readout (AMR)

Robust Metal Housing

Descrizione

Designed for UV microscopy, the edge^{plus} AM8517MT-FV is an 8-megapixel microscope featuring 395 nm LEDs. It offers exceptional image clarity and detail thanks to its enhanced sensitivity sensor and 32 levels of light intensity control. AM8517MT-FV features AMR to simplify measurements and is perfect for industrial inspections, forensic analysis, counterfeit detection, and other applications that require UV light.



Metal housing



Adjustable
~20x - 220x



8,0 Megapixels
3840 x 2160



UV-LEDs
390~400nm



Measurement
functionality



8 White LEDs
switchable



Automatic
Magnification
Reading (AMR)



Long working
distance

Working distance/field of view/depth of field

M	WD	FOV (x)	FOV (y)	DOF
20	57.5	30.35	17.07	6.60
30	31.8	20.23	11.38	3.16
40	19.7	15.17	8.53	1.90
50	13.0	12.14	6.83	1.30
60	9.0	10.11	5.69	0.96
70	6.6	8.67	4.88	0.74
80	5.2	7.59	4.27	0.60
90	4.4	6.74	3.79	0.50
100	4.0	6.07	3.41	0.42
110	4.0	5.52	3.10	0.37
120	4.3	5.06	2.85	0.32
130	4.7	4.67	2.63	0.29
140	5.3	4.34	2.44	0.26
150	6.0	4.05	2.28	0.23
160	6.8	3.79	2.13	0.21
170	7.6	3.57	2.01	0.20
180	8.6	3.37	1.90	0.18
190	9.6	3.20	1.80	0.17
200	10.6	3.03	1.71	0.16
210	11.7	2.89	1.63	0.15
220	12.8	2.76	1.55	0.14

Specifiche

Lighting	
Light/ LED type	UV Light (395 nm)
Number of LEDs	8
Optics	
Magnification	20x ~ 220x
Sensor	
Resolution	8.0 Megapixel (3840x2160)
Maximum frame rate	10 fps at 8.0 MP, MJPEG 25 fps at 2,0 MP, MJPEG
Compatibility	
Interface	USB 2.0
Operating system	Windows 10/11 macOS 10.14 or later

Housing	
Magnification lock	Yes
Dimensions	130 mm (H) x 32 mm (D)
Weight	117g
Cable length	1.8m
Features	
Special feature	Automatic Magnification Readout (AMR)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
Information	
Package contents	Microscope, carry pouch, calibration target, user manual, N3C-C (Close Cap) N3C-EB (Extended Open Black Cap) N3C-LB (Black Long Cap) N3C-OB (Black Open Cap)
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1100,00 - €1300,00