

AF7515MZT

Productcode: Af7515MZT - EDGE



Korte omschrijving

- High Optical Resolution
- 5.0 Megapixel
- Flexible LED Control (FLC)
- Adjustable Polarizer
- Automatic Magnification Reading (AMR)
- Adaptable Interface
- Robust Metal Housing

Omschrijving

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features such as flexible LED control (FLC), Automatic Magnification Reading (AMR) and full aluminum body, the Dino-Lite AF7515MZT is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite AF7515MZT offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Automatic
Magnification
Reading (AMR)



Adjustable
~10-220x



The AF7515MZT is part of the universal range and with its standard working distance and wide magnification range from 10 – 220x, it is suitable for a wide range of applications. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc. The AMR function is of particular importance when the measurement functions are frequently used.

The main features of the AF7515MZT are:

- 5 Megapixel Edge sensor
- 10-220x magnification
- Integrated polarizer
- Aluminum housing
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- Wireless Ready
- And more...

Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X) * Without front cap	FIELD OF VIEW(Y)	DEPTH OF FIELD Unit = mm
Listed values may differ slightly				
10	142.6	39.6	29.7	26.0
20	60.1	19.8	14.8	7.0
30	33.6	13.2	9.9	3.3

40	21.0	9.9	7.4	2.0
50	14.0	7.9	5.9	1.4
60	9.8	6.6	4.9	1.0
70	7.3	5.7	4.2	0.8
80	5.7	4.9	3.7	0.6
90	4.8	4.4	3.3	0.5
100	4.3	4.0	3.0	0.4
110	4.2	3.6	2.7	0.4
120	4.3	3.3	2.5	0.3
130	4.7	3.0	2.3	0.3
140	5.2	2.8	2.1	0.3
150	5.8	2.6	2.0	0.3
160	6.5	2.5	1.9	0.2
170	7.3	2.3	1.8	0.2
180	8.1	2.2	1.6	0.2
190	9.1	2.1	1.6	0.2
200	10.0	2.0	1.5	0.2
210	11.0	1.9	1.4	0.2
220	12.1	1.8	1.3	0.2

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Magnification	10x ~ 220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	5.0 Megapixel (2592x1944)
Maximale framesnelheid	30 fps
Compatibiliteit	

Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV (max 1.3MP)
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 (optional)
Behuizing	
Materiaal van de behuizing	Metal housing
Afmetingen	11.5cm (L) x 3.4cm (D)
Gewicht	97g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Automatic Magnification Reading (AMR), Flexible LED Control (FLC).
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	Yes
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€1000,00 - €1200,00