

AM4115-FIT

Merk:

Productcode: AM4115-FIT



Korte omschrijving

1.3 Megapixel resolution

~850nm IR LEDs

20-220x magnification

Versatility due to exchangeable caps

Omschrijving

The AM4115-FIT has special lighting with LED's emitting IR light around the 850 nm spectrum.



USB 2.0



Measurement
functionality



Adjustable
~20x-220x



Magnification
lock



1.3 megapixel
1280 x 1024



Infrared
LEDs ~ 850nm



Long working
distance

The Dino-Lite AM4115-FIT has special lighting with LED's emitting UV light around the 850 nm spectrum. The Dino-Lite Edge models provide superior image quality and a high level of flexibility due to the adaptable cap design.

» Also available with ~780nm or 940nm LEDs (model AM4115-FKT/FJT).


Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
--------------------	------------------	------------------	------------------	----------------

Listed values
may differ
slightly

20	60.2	19.5	15.6	2.5
30	33.5	13.0	10.4	1.8
40	20.9	9.8	7.8	1.5
50	13.9	7.8	6.3	-
60	9.7	6.5	5.2	-
70	7.1	5.6	4.5	1.0
80	5.5	4.9	3.9	-
90	4.5	4.3	3.5	-
100	4.1	3.9	3.1	-
110	4.0	3.6	2.8	-
120	4.1	3.3	2.6	-
130	4.5	3.0	2.4	-
140	5.0	2.8	2.2	-
150	5.6	2.6	2.1	-
160	6.3	2.4	2	-
170	7.1	2.3	1.8	-
180	8.0	2.2	1.7	-
190	8.9	2.1	1.6	-
200	9.9	2.0	1.6	-
210	10.9	1.9	1.5	-
220	11.9	1.8	1.4	0.1

Special Light





Specificatie

Verlichting	
Licht / LED-type	~850 nm Infrared
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR pass filter
Diffusor beschikbaar	No
Emissiefilter	No
Polarisator	No
Optiek	
Magnification	20x ~ 220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV

Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Vergrotingsslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)
Gewicht	105g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	No
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€500,00 - €700,00

Product galerij





AF4115ZT
w/o IR



AM4115-FIT or FJT
with IR 850nm or 940nm

