

AM4115TL - EDGE

Merk:

Productcode: AM4115TL



Korte omschrijving

1.3 Megapixel resolution

Versatility due to exchangeable caps

10-140x magnification

Long working distance

Omschrijving

The wide range of magnification (10-140x), the large field of view and working distance of up to 23 cm makes the AM4115TL the ideal solution for all situations where a longer distance between the microscope and the object is required or when it is needed to work under the microscope (repair, rework and assembly tasks etc.)

 USB 2.0	 Measurement functionality	 Continuous ~10x - 140x
 Magnification lock	 1.3 megapixel 1280 x 1024	 8 White LEDs switchable
 Long working distance	 Exchangeable cap	

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
Listed values may differ slightly	* With front cap			Unit = mm

10	227	39.0	31.2	12
20	105	19.5	15.6	4.5
30	65	13.0	10.4	3.1
40	47	9.8	7.8	1.8
50	36	7.8	6.2	1.2
60	30	6.5	5.2	0.9
70	26.2	5.6	4.5	0.6
80	23.8	4.9	3.9	0.5
90	22.4	4.3	3.5	0.37
100	21.7	3.9	3.1	0.28
110	21.6	3.5	2.8	0.22
120	21.8	3.3	2.6	0.17
130	22.3	3.0	2.4	0.12
140	23	2.8	2.2	0.09

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	No
Optiek	
Magnification	10x ~ 140x
Macro zoom	No
Werkafstand	Long
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0

Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Vergrotingsslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)
Gewicht	105g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	No
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€500,00 - €700,00

Product galerij

