

AM8517MZT

Productcode: AM8517MZT Edge Plus



Korte omschrijving

High Optical Resolution

8.0 Megapixel

Enhanced Flexible LED Control (eFLC)

Automatic Magnification Reading (AMR)

Robust Metal Housing

Omschrijving

Capture vibrant and true-to-life images with the 8-megapixel Dino-Lite AM8517MZT digital microscope. Including a polarizer and featuring AMR and eFLC, AM8517MZT provides the versatility to perform a variety of tasks.



Metal housing



Enhanced Flexible LED control



Adjustable
~10-220x




8,0 Megapixels
3840 x 2160



Measurement
functionality



8 White LEDs
switchable



Polarizer
anti-reflection



Automatic
Magnification
Reading (AMR)

The main features of the AM8517MZT are:

- 8 Megapixels
- High Optical Resolution
- Automatic Magnification Reading (AMR)
- Enhanced Flexible LED Control (eFLC)
- Adjustable Polarizer
- Robust Metal Housing
- 10x ~ 220x magnification (Edge shading occurs below 25x when previewing in 16:9 windows.)
- And more...

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	142.6	60.69	34.14	26.15
20	59.8	30.35	17.07	7.05
30	33.1	20.23	11.38	3.36
40	20.5	15.17	8.53	2.02
50	13.4	12.14	6.83	1.38
60	9.2	10.11	5.69	1.01
70	6.7	8.67	4.88	0.79
80	5.1	7.59	4.27	0.64
90	4.1	6.74	3.79	0.53
100	3.7	6.07	3.41	0.45
110	3.6	5.52	3.10	0.39
120	3.7	5.06	2.85	0.34
130	4.1	4.67	2.63	0.30
140	4.5	4.34	2.44	0.27
150	5.2	4.05	2.28	0.25
160	5.9	3.79	2.13	0.22
170	6.7	3.57	2.01	0.21
180	7.5	3.37	1.90	0.19
190	8.5	3.20	1.80	0.18
200	9.4	3.03	1.71	0.16
210	10.5	2.89	1.63	0.15
220	11.5	2.76	1.55	0.14

Listed values may differ slightly

* Without front cap

Unit = mm

Specification

Verlichting	
Licht / LED-type	White

Aantal leds	8
Optiek	
Magnification	10x ~ 220x
Werkafstand	142.6 ~ 11.5 mm
Sensor	
Sensortype	CMOS
Resolutie	8.0 Megapixel (3840x2160)
Maximale framesnelheid	10 fps at 8.0 MP, MJPEG 25 fps at 2.0 MP, MJPEG
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 10/11
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Behuizing	
Materiaal van de behuizing	Metal housing
Afmetingen	130 mm (H) x 33 mm (D)
Gewicht	120 g
Kenmerken	
Bijzonderheid	Auto and Manual Refocus
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
Informatie	
Inhoud van de verpakking	N3C-C (Close Cap) N3C-D (Diffuser Cap) N3C-D2 (Opal Diffuser Cap) N3C-E (Extended Open Cap) N3C-L (Long Cap) N3C-O (Open Cap) N3C-S (Sidelight Cap)
Garantie-informatie	2 years European warranty
Regulatory approval:	CE, FCC, ROHS
Prijsklasse	€1200,00 - €1400,00