

MSAK810



Merk: Dino-Lite
Productcode: MSAK810

Korte omschrijving

Flexible extension arm

Omschrijving

The MSAK810 adjustable flex arm which can be attached to the pole of a RK-06A/RK-06AE/RK-06F for additional hands free viewing angles with the Dino-Lite. The arm has a maximum of 30cm reach, and can be bent and twisted to attain your desired viewing positions.

The MSAK810 is a great addition to a RK-06A/RK-06AE/RK-06F allowing an in-depth visual inspection with multiple Dino-Lite's.

Specificatie

Compatibiliteit	
Compatibel met:	All Dino-Lite models
Behuizing	
Afmetingen	35.5cm (W) x 3.1cm (L)
Gewicht	181 g
Kenmerken	
ESD veilig	No
Informatie	
Inhoud van de verpakking	Stand, HD-P1 holder

Garantie-informatie	2 years European warranty
accessoires:	Professional stands
Prijsklasse	€50,00 - €150,00

Product galerij

