

WF4915ZTL



Merk:

Productcode: WF4915ZTL - Wireless

Korte omschrijving

1.3 Megapixel Edge sensor
Extended Depth of Field (EDOF)
Extended Dynamic Range (EDR)
Flexible LED Control (FLC)
Automatic Magnification Reading (AMR)

Omschrijving

The Dino-Lite WF4915ZTL is a Wireless model that is part of the Long Working Distance (LWD) series. Go from wireless to wired and back in an instant. Work wired via USB or work wireless with the attachable WF-20 Wireless adapter.



USB 2.0



1,3 Megapixels
1280 x 1024



Adjustable
~10x - 140x



Magnification
lock



Polarizer
anti-reflection



Long working
distance



Flexible LED
Control FLC



Exchangeable
cap



Automatic
Magnification
Reading (AMR)



Extended
Depth Of Field
EDOF



Extended
Dynamic
Range EDR



Wireless

The WF4915ZTL is equipped with premium features such as Extended Depth of Field (EDOF), Extended Dynamic Range (EDR), Flexible LED Control (FLC), integrated polarizer, extensive measurement functionality and Automatic Magnification Reading (AMR) for measurement-intensive applications.

The main features of the WF4915ZTL are:

- Completely wireless solution (including WF20)
- 10-140x magnification
- 1.3 Megapixel Edge sensor
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- Automatic Magnification Reading (AMR)
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

*(*EDOF/EDR only functions under Windows OS)*

Working distance/field of view/depth of field

Magnification Rate	Working Distance *	Field of View(x)	Field of View(y)	Depth of Field
Listed values may differ slightly	* Without front cap			Unit = mm
10	234.5	39.0	31.2	12
20	112.5	19.5	15.6	4.5
30	72.5	13.0	10.4	3.1
40	54.5	9.8	7.8	1.8
50	43.5	7.8	6.2	1.2
60	37.5	6.5	5.2	0.9
70	33.7	5.6	4.5	0.6

80	31.3	4.9	3.9	0.5
90	29.9	4.3	3.5	0.37
100	29.2	3.9	3.1	0.28
110	29.1	3.5	2.8	0.22
120	29.3	3.3	2.6	0.17
130	29.8	3.0	2.4	0.12
140	30.5	2.8	2.2	0.09

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR-afsnijfilter > 650 nm
Diffusor beschikbaar	Ja (inclusief N3C-D)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Magnification	10x ~ 140x
Macro zoom	No
Werkafstand	Lang
Type lens	Glas met antireflectiecoating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only)
Software	DinoCapture 2.0 (Windows) cable + wireless, DinoXcope (Mac OS) cable only, DinoConnect wireless only
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde	MOV

videoformaten (MacOS)	
Beeldvormingsnormen	DirectShow, UVC
Wifi	Yes
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Vergrotingsslot	Yes
Afmetingen	11.4cm (L) x 3.3cm (D)
Gewicht	111g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Automatic Magnification Reading (AMR), Extended Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC)
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
Informatie	
Inhoud van de verpakking	Microscope, WF-20, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS, UKCA – available upon request – marketing@dino-lite.eu
Prijsklasse	€1100,00 - €1300,00

Product galerij

