

# AM7915MZT

**Brand:**

**Product Code:** AM7915MZT




## Short Description

5 Megapixel resolution  
Extended Depth of Field (EDOF)  
Extended Dynamic Range (EDR)  
Flexible LED Control (FLC)  
10-220x magnification

## Description

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features, the Dino-Lite AM7915MZT is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite AM7915MZT offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Adjustable  
~10-220x



5 megapixel  
2592 x 1944



Standard working  
distance



Measurement  
functionality



Extended  
Depth Of Field  
EDOF



With the Extended Dynamic Range (EDR) feature, the details of darker or brighter areas within the object can be revealed by stacking images at different exposure levels. The Extended Depth of Field (EDOF) feature automatically stacks images at different focus level to improve the depth of field on rough or uneven surfaces. With the built-in Automatic Magnification Reading (AMR), measurements can be performed easily and quickly. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

**The main features of the AM7915MZT are:**

- 5 Megapixel Edge sensor
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- 10-220x magnification
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

*(\*EDOF/EDR only functions under Windows OS)*

**Working distance/field of view/depth of field**

| <b>MAGNIFICATION RATE</b> | <b>WORKING DISTANCE *</b> | <b>FIELD OF VIEW(X)</b> | <b>FIELD OF VIEW(Y)</b> | <b>DEPTH OF FIELD</b> |
|---------------------------|---------------------------|-------------------------|-------------------------|-----------------------|
| 10                        | -                         | 142.6                   | 39.6                    | 29.7                  |
| 20                        | 52.7                      | 60.1                    | 19.5                    | 15.6                  |

|                                                              |      |      |     |                  |
|--------------------------------------------------------------|------|------|-----|------------------|
| <b>30</b>                                                    | 33.5 | 13.0 | 9.7 | 1.8              |
| <b>40</b>                                                    | 20.9 | 9.8  | 7.3 | 1.5              |
| <b>50</b>                                                    | 13.9 | 7.8  | 5.8 |                  |
| <b>60</b>                                                    | 9.7  | 6.5  | 4.8 |                  |
| <b>70</b>                                                    | 7.1  | 5.6  | 4.2 | 1.0              |
| <b>80</b>                                                    | 5.5  | 4.9  | 3.6 |                  |
| <b>90</b>                                                    | 4.5  | 4.3  | 3.2 |                  |
| <b>100</b>                                                   | 4.1  | 3.9  | 2.9 |                  |
| <b>110</b>                                                   | 4.0  | 3.6  | 2.7 |                  |
| <b>120</b>                                                   | 4.1  | 3.3  | 2.4 |                  |
| <b>130</b>                                                   | 4.5  | 3.0  | 2.2 |                  |
| <b>140</b>                                                   | 5.0  | 2.8  | 2.1 |                  |
| <b>150</b>                                                   | 5.6  | 2.6  | 1.9 |                  |
| <b>160</b>                                                   | 6.3  | 2.4  | 1.8 |                  |
| <b>170</b>                                                   | 7.1  | 2.3  | 1.7 |                  |
| <b>180</b>                                                   | 8.0  | 2.2  | 1.6 |                  |
| <b>190</b>                                                   | 8.9  | 2.1  | 1.5 |                  |
| <b>200</b>                                                   | 9.9  | 2.0  | 1.5 |                  |
| <b>210</b>                                                   | 10.9 | 1.9  | 1.4 |                  |
| <b>220</b>                                                   | 11.9 | 1.8  | 1.3 | 0.1              |
| <b>Listed values may differ slightly * Without front cap</b> |      |      |     | <b>Unit = mm</b> |

## Specification

| Lighting               |                                    |
|------------------------|------------------------------------|
| Light/ LED type        | White                              |
| Number of LEDs         | 8                                  |
| LED on/off switchable: | Yes                                |
| Infrared filter        | IR cut-filter >650 nm              |
| Diffuser available     | Yes (N3C-D included)               |
| Emission filter        | No                                 |
| Polarizer              | Yes, linear                        |
| Optics                 |                                    |
| Magnification          | 10x ~ 220x                         |
| Macro zoom             | No                                 |
| Working distance       | Standard                           |
| Lens type              | Glass with anti-reflection coating |
| Sensor                 |                                    |
| Sensor type            | CMOS                               |

|                                   |                                                                                                                                                                                                                                  |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Resolution                        | 5.0 Megapixel (2592x1944)                                                                                                                                                                                                        |
| Maximum frame rate                | 30 fps                                                                                                                                                                                                                           |
| Compatibility                     |                                                                                                                                                                                                                                  |
| Interface                         | USB 2.0                                                                                                                                                                                                                          |
| Operating system                  | Windows 7, 8, 10 & 11, MacOS 10.9 and up                                                                                                                                                                                         |
| Software                          | DinoCapture 2.0 (Windows), DinoXcope (Mac OS)                                                                                                                                                                                    |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX                                                                                                                                                            |
| Supported video formats (Windows) | WMV, FLV, SWF                                                                                                                                                                                                                    |
| Supported image formats (MacOS)   | PNG, JPEG                                                                                                                                                                                                                        |
| Supported video formats (MacOS)   | MOV (max 1.3MP)                                                                                                                                                                                                                  |
| Imaging standards                 | DirectShow, UVC                                                                                                                                                                                                                  |
| Wifi                              | Wireless-ready, requires the WF-10 WiFi streamer (optional)                                                                                                                                                                      |
| Housing                           |                                                                                                                                                                                                                                  |
| Housing material                  | Metal housing                                                                                                                                                                                                                    |
| Magnification lock                | Yes                                                                                                                                                                                                                              |
| Dimensions                        | 10.5cm (L) x 3.2cm (D)                                                                                                                                                                                                           |
| Weight                            | 138g                                                                                                                                                                                                                             |
| Cable length                      | 1.8m                                                                                                                                                                                                                             |
| Features                          |                                                                                                                                                                                                                                  |
| Special feature                   | Automatic Magnification Reading (AMR), Extended Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC).                                                                                                 |
| Measurement                       | Yes                                                                                                                                                                                                                              |
| Calibration                       | Yes                                                                                                                                                                                                                              |
| Microtouch sensor                 | Yes                                                                                                                                                                                                                              |
| ESD safe                          | Yes                                                                                                                                                                                                                              |
| Information                       |                                                                                                                                                                                                                                  |
| Package contents                  | Microscope, carry pouch, software CD, calibration target, user manual, N3C-C (Close Cap), N3C-D (Diffuser Cap), N3C-D2 (Opal Diffuser Cap), N3C-E (Extended Open Cap), N3C-L (Long Cap), N3C-O (Open Cap), N3C-S (Sidelight Cap) |
| Warranty information              | 2 years European warranty                                                                                                                                                                                                        |
| Regulatory approval               | CE, FCC, ROHS                                                                                                                                                                                                                    |
| Price range                       | €1100,00 - €1300,00                                                                                                                                                                                                              |

## Product Gallery



