

AF4115ZT



Marka:
Ürün Kodu: AF4115ZT

Short Description

1.3 Megapixel Edge sensor
20x ~ 220x magnification
Adjustable Polarizer
Flexible LED Control (FLC)
Extensive measurement functionality

Açıklama

The Dino-Lite AF4115ZT is part of Universal series and connects to your device via USB. The AF4115ZT is Wireless-ready, but requires the (optional) [WF-20](#) to make it a fully wireless solution.

 USB 2.0	 1,3 Megapixels 1280 x 1024	 Adjustable ~20x - 220x
 Polarizer anti-reflection	 Measurement functionality	 Flexible LED Control FLC
 Magnification lock	 Standard working distance	 Exchangeable cap

The AF4115ZT is equipped with premium features such as Flexible LED control (FLC),

integrated polarizer, extensive measurement functionality.

The main features of the AF4115ZT are:

- Wireless-ready, requires the WF-20 adapter (optional)
- 20x ~ 220x magnification
- 1.3 Megapixel Edge sensor
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	60.2	19.5	15.6	2.5
30	33.5	13	10.4	1.8
40	20.9	9.8	7.8	1.5
50	13.9	7.8	6.3	
60	9.7	6.5	5.2	
70	7.1	5.6	4.5	1.0
80	5.5	4.9	3.9	
90	4.5	4.3	3.5	
100	4.1	3.9	3.1	
110	4	3.6	2.8	
120	4.1	3.3	2.6	
130	4.5	3	2.4	
140	5	2.8	2.2	
150	5.6	2.6	2.1	
160	6.3	2.4	2	
170	7.1	2.3	1.8	
180	8	2.2	1.7	
190	8.9	2.1	1.6	
200	9.9	2	1.6	
210	10.9	1.9	1.5	
220	11.9	1.8	1.4	0.1
Listed values may differ slightly	* Without front cap			Unit = mm

Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.12 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
Housing	
Housing material	Composite/ plastic housing
Dimensions	11.4cm (L) x 3.3cm (D)
Weight	111g
Cable length	1.8m
Features	
Special feature	Flexible LED Control (FLC)

Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
Information	
Package contents	Microscope, Carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€500,00 - €600,00

Product Gallery